

Prostal Limited.

1F., No.40, Aly. 22, Ln. 143, Ruiping Rd., Yangmei Disty, Taoyuan City 32658, Taiwan

TEL: +886-3-4828372 Fax: +886-3-4828377

URL: www.prostal.com.tw E-MAIL: joan@prostal.com.tw

Optical Variable Attenuator -----PJ3303

PJ3303 handhold optical variable attenuator is used for continuously variable optical signal attenuation. As the attenuator is used in the laser system for the on-line testing, therefore, PJ3303 can be used in the digital system of communication devices (such as: GPON,

PHD, SDH) and also in the system of adopting analog modulation (CATV)


Main Features

- stepwise attenuating by circumgyrated dial: attenuating step 0.05dB
- Provide with the function of displaying dB and dBm attenuating value
- 10 minutes Auto-off function can be activate and deactivate with keypad operation.
- After off the instruments, the system will have the memorizing of the attenuating value and the attenuating step, in order to restore the system back to the previous shut down state when open the instruments next time
- Portable, rugged, lightweight; Easy to use.

Applications

- Telecom Maintenance
- CATV Maintenance
- Comprehensive cable construction system
- Optical instruments research and development
- Optical communication education and lab testing
- Other optical project

Specifications





Vat number: 24849130

Prostal Limited. P1/1